

Pinnacle SL300 Straight Stair Lift EVALUATION/ORDER FORM



Date	□ Quote □ Order
Sales Representative	Account Number
Dealer	Purchase Order Number
Address	Shipping: ☐ Pick-up ☐ Fed Ex ☐ Palletized (premium)
CityStateZip	Ship To Address
Phone	
Fax	
Email	Contact
Opportunity Reference / Project Name	Phone
	Projected Close Date
CONF	IGURATION
QTY SL300 Std. 15'6" Rail	QTY SL300FR – LH Folding Rail, Left Hand, 15'6" Rail
QTY SL300COS, w/Chassis Obst. Sensors, 15'6" Rail Straight	QTY SL300FR – RH Folding Rail, Right Hand, 15'6" Rail
TRACK, PA	RTS & OPTIONS
Track	Parts & Options
QTYSL600T3 – 3' Mid Section Assembly w/brackets	QTYSL305 – Key Lock on Lift (chassis)
QTYSL600T5 – 5' Mid Section Assembly w/brackets	QTYSL600SB1 – Additional Short Brackets
QTYSL600T8 – 8' Mid Section Assembly w/brackets	QTYSL600TB1 – Additional Tall Brackets
[] SL600C – Custom CutFt in length (including overrun)	QTYSL600CC8 – 8' Charger Cord Extension
single unit orders only. Must include additional mid-section(s) above if total above 15'6".	QTYSL300RET – Retractable Seat Belt (DIr Install)
How To	O MEASURE
П	Measurements
a a	A to B - Inches from top landing to bottom floor
RISE	A to H - Inches from top landing to nearest obstruction - for example, a door
TREAD 20,16	Rise Inches Tread Inches WidthInches
Rige 19.33	7" Overrun recommended if top landing is clear (This is added to the A to B)

NOTE: If A to H is < 13", must order tall bracket.

Notes



Home Modification Occupational Therapy Alliance